


## LED-INDICATOR WHITE


LED 10mm - 24V DC - 20 mA - IP67

(white)  
24 V DC

### [Link to Product](#)

#### Illustration





Product may differ from Image

#### Technical Data

Operating voltage	24 V DC $\pm 15\%$
Current consumption	approx. 15 mA
Protection acc. to (IEC 60529/EN 60529)	IP67

#### General data

Housing	Brass, chrome plated
LED $\varnothing$	10 mm
Front panel hole diameter $\varnothing$	14 mm
Dimensions H x W x D	16x16x45 mm
Temperature range	-40...+70 °C
Connection	Faston 2.8 x 0.8 mm

#### Commercial data

country of origin	DE
customs tariff number	85414010
minimum order quantity	10