



Article number		
LV short text		00102

Technical Data		
Operating current rated value	A	10
Operating voltage rated value maximum	V	230
Switching capacity active power	W	3 680
Switching capacity current	A	10
Number of switching outputs maximum		12
Suitability for use switching of C load		Yes
Suitability for operation Multiphase operation		Yes
Mounting type		modular installation device
Product extension can be installed supplementary devices		No
Product function direct operation		Yes
Number of width units		12
Protection class IP		IP20
Display version LED		No
Number of digital inputs		0
Bus coupling Integrated		Yes

## Certificates/approvals

<b>General Product Approval</b>	<b>Declaration of Conformity</b>	<b>other</b>
---------------------------------	----------------------------------	--------------

[Miscellaneous](#)



EG-Konf.

[Environmental Confirmations](#)

## Further information

**Gamma-TD (Tech. Documentation, ETS Product database, Invitation to tender text)**

<http://www.siemens.com/gamma-td?ssn=5WG1532-1DB61>

**Gamma - Catalogue**

<http://www.siemens.com/gamma-catalogue>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=5WG1532-1DB61&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=5WG1532-1DB61&lang=en)

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5WG1532-1DB61>

last modified:

08/08/2017