

HEATER DC 24V, 60 W HG140 14013.0-00



Figure similar

Model		
product brand name		SIVACON
Product designation		semiconductor heater unit
General technical data		
Active power consumption / Rated value	W	60
Voltage		
Continuous heat output / at 20 °C	W	75
Inrush current / typical	A	0
Protection class		
Protection class IP		IP20
Main circuit		
Operating voltage		
• Rated value / minimum	V	12
• Rated value / maximum	V	30
• with AC / at 50 Hz / Rated value / maximum	V	24
• with AC / at 60 Hz / Rated value / maximum	V	24
Product details		
Product component		
• blower		No
• Thermostat		No
Mechanical Design		
Height	mm	185

Width	mm	70
Depth	mm	50

Certificates

Equipment marking

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

R
E

General Product Approval

Declaration of Conformity



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8MR21306BA>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/8MR21306BA/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR21306BA

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015