




Datenblatt - Fiche technique - Data sheet


11.02.8908



ROLINE USB 2.0 Kabel, Typ A-A, 0,8m

ROLINE Câble USB 2.0 Type A-A, 0,8m

ROLINE USB 2.0 Cable, A - A, M/M, 0.8 m




JACKET PRINTING: USB SHIELDED HIGH SPEED CABLE 2.0 REVISION
28AWG/1P+24AWG/2C E314459 兪 AWM 2725 80℃ 30V VW-1

NOTE:


1. CABLE: UL2725,AL+B-FOIL,28AWG*1P+24AWG*2C,BLACK COLOR,OD=5.0mm,PVC JACKET.
(AL/MG 65%,double shielded, bare copper conductor,)(NOTE: USB2.0 WIRE MATERIAL).
2. LENGHT: 800mm.
3. CONNECTORS: USBM(A)*2PCS(WHITE INSULATOR)(SHELL NICKEL)(PIN GOLD FLASH 30U”).
4. MOLD:MOLDING USBAM TYPE.
5. CONTACTS:

1	2	3	4	64
1	2	3	4	64



- WHITE/GREEN PAIR...28AWG , RED/BLACK...24AWG
6. OPEN/SHORT TEST: 100% TEST.
 - A.100% OPEN,SHORT&INTERMITTANCE TEST.
 - B.CONDUCTOR RESISTANCE: 3ohms MAX.
 - C.INSULATION RESISTANCE: 5M Min/,10ms:
 7. ALL MUST BE ROHS COMPLIANT.

PE BAG(100*200*0.06)ROLINE HEADER+EAN STICKER



COMPANY	RLA	ITEM NO.	11.02.8908	NO	B4647	Parts Name	USBAM-USBAM	SCALE	NON
REVISION	DATE	DESCRIPTION		SPEC				UNIT(mm)	
REV./A/0	2012.05.08							PAGE	
DRAWN BY		DESIGNED BY		Rotronic Co.,Ltd.					
APPROVAL BY									