

## **DA441**

24V DC 16A power supply Within a 19" 2U Rack-mount enclosure

19" rack mountable power supplies with 24V AC 16A outputs individually fused with indication. Typical uses include powering CCTV cameras, camera housing heaters.

Output			
	DA441-8	DA441-16	
Voltage	24V AC	24V AC	
Current	8 x 2A	16 x 1A	
Connection type	PCB terminal block (2.5mm²)		
Fused	20 x 5mm 2A quick blow glass fuse		
Input			
	DA441-8 DA441-16	DA441-8-110V DA441-16-110V	
Voltage	230V AC @ 50Hz (+/- 10%)	110V AC @ 50Hz (+/- 10%)	
Power consumption	< 500VA		
Connection type	C14 IEC connector (Kettle lead)		
Fused	6.3A Mains fuse (BS1362)		
Mains on indication	Neon lamp		
Environmental			
Operating temperature	-10°C to +40°C		
Storage temperature	-20°C to +50°C		
Operating relative humidity	Maximum 95% non-condensing		
Dimensions*			
Width	478mm (19" Rack-mount)		
Height	89mm (2U Standard rack-mour	89mm (2U Standard rack-mount)	
Depth	248mm		
Weight	< 7.4Kg		
Enclosure material	Mild steel		
Finish	Powder coated black semi-gloss		
Other			
Estimated operations before failure (MTBF)	65,000 hours		
CE Approved	Yes		
		*(+/- 2mm)	

\*(+/- 2mm)