

Product information

97 53 18

KNIPEX Twistor®16

Self-Adjusting Crimping Pliers for wire ferrules With rotatable die head



• Crimp head can be rotated 360°, with 8 locking positions

- Square crimp profile, high capacity range from 0.14 to 16 mm²
 Wire ferrules can be crimped from almost any working position
- Crimping pliers adjust automatically to different cross-sections
- Crimp opening accessible from both sides, extra-long wire ferrules can be fed in
- Crimping of Twin wire ferrules up to 2 x 6 mm² possible
- Repetitive, high crimping quality due to ratchet mechanism (unlockable)
- Light and handy tool, manual force reinforced by toggle lever mechanism
- Special quality chrome vanadium electric steel, oil-hardened

MM 🌄 🥔 🥔 💋

General	
Article No.	97 53 18
EAN	4003773082729
Pliers	chrome-plated
Head	chrome-plated
Handles	with multi-component grips
Weight	478 g
Dimensions	200 x 80 x 26 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable
Technical details	

- ·	
Application	Wire ferrules
Capacity in square millimetres	0.14 — 16 mm²
AWG	26 — 6
Number of crimping positions	1

technical change and errors excepted





Uniquely flexible: connectors can be inserted in the rotatable crimp head from almost any position



Twin wire ferrules up to 2 x 6 mm² can be crimped without adjustment







KNIPEX Quality – Made in Germany





Crimp head can be rotated 360° for optimal accessibility, even in confined spaces