


Material:	Messing vernickelt
max. Betriebsdruck:	18 bar
max. Betriebstemperatur:	200 °C
verwendbare Schläuche:	PA, PE, PU



11.300-8-E

## Gerade Verbinder

Typen Nr.	Artikel Nr.	ØD	L	 1	 2	 3	O-Ring
11.300-5-E	114758	5/3	28,5	8	8	8	ohne
11.300-6-E	114759	6/4	34,5	12	12	12	ohne
11.300-8-E	114760	8/6	35,0	14	14	14	ohne
11.300-10-E	114756	10/8	38,0	16	14	16	ohne
11.300-12-E	114757	12/10	41,0	18	17	18	ohne