

Adjustable clamps

Short and infinitely adjustable with U-piece



Application:

For clamping workpieces.

Version:

- With U-piece
- Suitable for tough conditions, e.g. on presses
- Tempered
- Galvanised and blue passivated
- Infinitely adjustable

Delivery:

With U-piece, though without clamping screw



Art. no.	26225 030
For table grooves according to DIN 650	20 mm, 22 mm
Min./max. clamping height	0-65 mm
Min./max. clamping height 2	50-100 mm
Clamping shoe length	144 mm
Clamping shoe width	66 mm
Bore diameter	22 mm
Distance 2	80 mm
Distance	32 mm
Distance 1	46 mm
Distance 3	20 mm
Suitable screw DIN 787	M20 x 200 mm
Slot nut width of clamping screw	20 mm, 22 mm
Height	100 mm

EAN-Code

4020772073954