

# FELLER GMBH

A-2525 GUENSELSDORF, AUSTRIA - TEL.: .. 43(2256) 62 32 50 - FAX: .. 43 (2256) 62 32 57  
e-mail: sales@feller-at.com <http://www.feller-at.com>

## **Description: 12G-H05VVF3G075-C13/2,00M SW9005**

Rating of cord set: 10A/250Vac

### **1. PLUG: Type 12G**

Molded plug according to : SEV 1011:2009, chapter SEV 6534/2  
Rated current and voltage : 10A, 250 V AC  
Plugbase : thermoplastic Polyester (PBTP) GFR  
Pins : brass, part-insulated, nickel-plated, crimped  
Pins outer diameter : 4,0 mm  
Outer mold : PVC compound, hardness Shore A75-77  
Approvals : SEV

### **2. CORD: Type H05VVF3G075 mm<sup>2</sup> BLACK**

Flexible cord according to : EN50525-1, EN50525-2-11, EN50395, EN50396, AS3191  
Marked : \*JF\*<ÖVE><HAR>H05VVF3G0,75mm<sup>2</sup>\*N1095\*CE \* CCC 60227  
IEC 53 (RVV) 300/500V 3x0,75 \* KTL SW01001-2001A  
Number of cores : 3  
Conductor construction : 23 x 0,20 mm O.D. 1,09 mm  
Conductor insulation : Extruded PVC, O.D. 2,30 mm  
Jacket : Extruded PVC, O.D. 6,60 mm +/- 0,20mm  
Resistance of conductors : max. 26 Ω/km  
Dielectric strength : 2kVac, 1min.  
Insulation resistance : >0,010 MΩ/km  
Color of conductors : yellow/green, brown, blue  
Approvals : HARMONIZED, ÖVE

### **3. CONNECTOR: Type C13**

Molded connector according to : EN/IEC60320/C13,  
Rated current and voltage : 10 A, 250 V AC  
Construction : double insulation  
Contacts of the connection : self-adjusting phosphor bronze CuSn6  
Inner insulation : PPO GFR  
Outer mold : PVC compound, hardness Shore A 75-77  
Approvals : CE, ENEC


**Environmental conformity** : EU-Directive 2012/19/EU (WEEE)  
EU-Directive 2011/65/EU  
EU-Directive 1907/2006 EG (REACH -compliant)

### **TESTING**

Electrical testing : 100%  
Visual inspection : 100%  
High pot test wire to wire : 3kVac for 2 sec.  
Continuity test : 25Aac to grounding / 20Aac to line and neutral  
Polarity test : yes  
Skin high pot test : 6kVac line to skin

design subject to change without prior notice, except written agreements with customer

DATE of ISSUE:	September, 2018
REV: 1	ORIG: DG



1.  
12G

2.  
H05VVF3G075

3.  
C13

**Feller Type: 12G-H05VVF3G075-C13/2,00M SW9005**

PN: 143-30-654

**All dimensions in mm**

24.09.2018 **DG**

**RoHS compliant**

**FELLER**   
 A-2525 Günselsdorf, Austria  
 Telefon 0043-2256-62325-0  
 Fax: 0043-2256-62325-7  
 email: sales@feller-at.com  
 http://www.feller-at.com