
## COMUS Group



Part Number: RSH-33 Magnet - Bare Product Data Sheet



## **✓ RoHS** Compliant

Drawings not to scale. All dimensions in inches (mm) nominal.

SPECIFICATION	
Туре	Rectangular
Magnet Material	Alnico/Alcomax
Typical Gauss reading, direction A at 3mm	200 - 250
Operating temperature max.	550°C
Length	0.768"
Height	0.126"
Width	0.126"

Alnico/Alcomax is a good general purpose material that can be machined or cast to the required shape before magnetizing. The material has the best temperate coefficient of all permanent magnets. The high nickel content results in good corrosion and oxidisation resistance.

As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to help you with the latest information on this product range and the details of our full design and manufacturing service. All products are supplied to our standard conditions of sale unless otherwise agreed in writing.

Phone: (1) 973 777 6900

## www.comus-intl.com

## Fax: (1) 973 777 8405

Belgium: + 32 (0)12 390400 - Assemtech, UK: +44 (0) 1255 862236 - Germany: +49 (0)911 923 15 943 ©2012 Copyright Comus International, 454 Allwood Road, Clifton NJ 07012, USA