

SVS VALVE PLUG FORM A 18MM FIELD-WIREABLE


24...230V LED PG9 Bridge Rectifier



Form A (18 mm)
24...230 V AC/DC
LED and bridge rectifier
PG 9

Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)

Illustration



stay connected

Height: 41 mm

Product may differ from Image

Approvals



Form

29541

Technical Data

| | |
|--------------------------------|---|
| Operating voltage | 24...230 V AC/DC |
| Operating current per contact | max. 1.5 A |
| Connection cross section | 4 mm ² single core, with ferrule end 1.5 mm ² |
| Sealing range (cable diameter) | 6...8 mm |
| Locking of ports | M3 (recommended torque 0.4 Nm) |
| Compression gland | PG 9; (PG11, NPT 1/2" on request) |
| Protection | IP65 inserted and tightened (EN 60529), with gland |

General data

| | |
|-------------------|--------------|
| Temperature range | -20...+60 °C |
|-------------------|--------------|

Commercial data

| | |
|------------------------|----------|
| country of origin | CZ |
| customs tariff number | 85369010 |
| minimum order quantity | 1 |