



LED COVER FOR POSITION SWITCH PLASTIC
3SE52, FOR HOUSING ACC. TO EN50047,31MM
LEDS 110-230V AC YELLOW/GREEN TURQUOISE

Product designation		cover with LEDs 230 V AC, for EN 50047 enclosures, plastic, turquoise
General technical data:		
Shock resistance		30g / 11 ms
Vibration resistance		0.35 mm / 5g
Protection class IP		IP65
Explosion protection category for dust		none
Explosion protection category for gas		none
Enclosure:		
Design of the housing		block, narrow
Coating of the enclosure		Other types
Drive Head:		
Design of the operating mechanism		without
Communication/ Protocol:		
Design of the interface		without
Ambient conditions:		
Ambient temperature		
• during operation	°C	-25 ... +60
• during storage	°C	-40 ... +90
Supply voltage:		
Type of voltage of the supply voltage		
• of the optional LED indicator		AC
Supply voltage		

• of LED

V 230

Installation/ mounting/ dimensions:

mounting position	any
Mounting type	screw fixing

Certificates/ approvals:

General Product Approval	Declaration of Conformity	Test Certificates	other
 CSA	 UL		 EG-Konf.
		Special Test Certificate	Confirmation

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=3SE52303AA00>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3SE52303AA00/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mfb=3SE52303AA00&lang=en



last modified:

16.03.2015