

- Warm White
- Neutral White
- Cold White
- Amber
- Red
- Green
- Blue



## FEATURES

- Mercury free, no UV or IR emissions.
- DC12V
- 12watts/m
- 5000Hrs LED life time
- Dimmable
- CE,Rohs,UL,cUL

## SPECIFICATIONS

Length	5 meters/Roll
Power	12watts/m
Width	8mm
LED Qty	60LED/m
Input Voltage	12VDC
Lumen	20~22lm/LED
PCB	2 OZ
CRI	80+
Waterproof	IP20/IP65/IP67

## STRUCTURE

