


ROLINE UTP Patch Cord, Cat.6, black, 0.5 m

| | |
|---------------------------|---------------|
| Product No. | 21.15.1525 |
| Manufacturer | ROLINE |
| Manufacturer No. | 21.15.1525 |
| EAN (single piece) | 7611990156245 |



Cat.6

U/UTP

Patch cable for networking connections between devices. Prepared unshielded Twisted Pair cable with RJ-45 connectors on both ends. Durable due to moulded kink protection. Flexible cable, suitable for narrow bending. High quality plugs with gold plated contacts. Contact settings 1:1, in accordance with the EIA/TIA 568 standard. Construction: 4-pair stranded copper wire.

For a structured cabling system we recommend to use the following components: ROLINE Cat.6 UTP Cable, Solid Wire, AWG23: 21.15.0990 (100 m), 21.15.0991 (300 m); ROLINE Cat.6 Flush Mount Wall Jack, unshielded: 25.16.8494 (white), 25.16.8500 (ivory); ROLINE Cat.6 Surface Mount Wall Jack, unshielded: 25.16.8394 (white), 25.16.8395 (ivory); ROLINE Cat.6 19" Patch Panel, 24 Ports, unshielded: 26.11.0355 (light grey), 26.11.0362 (black); ROLINE Cat.6 UTP Patch Cord, grey, 5 m: 21.15.0935. The accredited German laboratory GHMT has tested and certified this product combination, in a Channel of 100 meters, as being compliant to Class E specifications; certificate no. z2329b-10-E (with flush mount)/z2330b-10-E (with surface mount).

Technical specifications

| | |
|---------------|--------------------|
| Manufacturer | ROLINE |
| Product group | Twisted Pair Cable |

| | |
|---------------------|------------------|
| Product type | UTP Patch Cables |
| Colour | black |
| Length | 0.5 m |
| Shield type | UTP |
| Transfer quality | Cat6 / Class E |
| Impedance | 100 Ohm |
| Quantity of wires | 8 |
| Conductor type | Wire |
| Crossed | No |
| Colour (Spout) | black |
| Cable LSOH | No |
| Connector Type RJ45 | Standard |