

## CTAM20C2



Article Number: 151-31201

Cable Tie Anchor Mount, 0.2" Hole Dia., 0.2" Max Tie Width, PA66, Black, 100/pkg



Download spec sheet

### Base Data

<b>Local Order Number</b>	CTAM20C2
<b>Type</b>	CTAM2
<b>Color</b>	Black (BK)
<b>Features and Benefits</b>	<ul style="list-style-type: none"> <li>• 4-way entry allowing the cable tie to secure bundles running parallel or perpendicular.</li> <li>• Secures with a single screw providing quick installation.</li> </ul>
<b>Product Description</b>	HellermannTyton cable tie anchor mounts are designed with a 4-way entry allowing the cable tie to secure bundles running parallel or perpendicular. The mounts are installed quick and easy by securing a single screw.
<b>Short Description</b>	Cable Tie Anchor Mount, 0.2" Hole Dia., 0.2" Max Tie Width, PA66, Black, 100/pkg

### Product Dimensions

<b>Length L (Imperial)</b>	0.8 "
<b>Length L (Metric)</b>	20.4 mm
<b>Fixation Method</b>	Screw Mounting and Rivet
<b>Width W (Imperial)</b>	0.4 "
<b>Width W (Metric)</b>	10.2 mm
<b>Cable Tie Width Max. (Imperial)</b>	0.2 "
<b>Cable Tie Width Max. (Metric)</b>	5.0 mm
<b>Height H (Imperial)</b>	0.2 "
<b>Height H (Metric)</b>	5.1 mm
<b>Height H2 (Imperial)</b>	0.05 "
<b>Height H2 (Metric)</b>	1.78 mm
<b>Mounting Hole Diameter D (Imperial)</b>	0.2 "
<b>Mounting Hole Diameter D (Metric)</b>	5.2 mm
<b>Mounting Hole Diameter D Max. (Metric)</b>	5.2 mm
<b>Mounting Hole Diameter D Min. (Metric)</b>	5.2 mm

### Logistics and Packaging

<b>Quantity Per</b>	bag
<b>Package Quantity (Metric)</b>	100
<b>Carton Quantity</b>	15000

### Material and Specifications

<b>Material</b>	Polyamide 6.6 (PA66)
<b>Material Shortcut</b>	PA66

**Flammability** UL94 V2  
**Operating Temperature** -40°F to +185°F (-40°C to +85°C)  
**ROHS Compliant** Yes  
**Certification/Specification** UL  
**UL Listed (US and Canada)** No  
**UL Recognized (US and Canada)** Yes