

Product information

97 52 50

KNIPEX PreciForce®

Crimping Pliers



- Consistently high crimping quality thanks to precision dies and ratchet mechanism (unlockable)
- Tools have been set precisely (calibrated) in the factory
- Optimum transmission of force thanks to toggle lever for fatiguereduced operation
- Good handling thanks to favourable handle position, low weight, compact design and ergonomically shaped handles
- Special quality chrome vanadium electric steel, oil-hardened

MM	
----	--

General	
Article No.	97 52 50
EAN	4003773051916
Pliers	burnished
Handles	with multi-component grips
Weight	498 g
Dimensions	220 x 70 x 21 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

Technical details







Application	Coax-, BNC- and TNC-connectors for RG 58/174/188/316
Number of crimping positions	6
Capacity SW mm	0.72 / 1.07 / 1.72 / 3.25 / 4.52 / 5.4 mm
Sleeves (diameter)	Ø 0.95 / 1.3 / 2.1 / 3.9 / 5.4 / 6.4 mm

technical change and errors excepted