

Magnetic Buzzer- 41.S78P030A-LF



■ MT Buzzer Single 3VDC Noryl

■ Colour - Black



General Specification

Model Number	41.S78P030A-LF
Operating Voltage Range (VDC)	2.0~ 5.0
Rated Voltage (VDC)	3
Max. Rated Current* (mA)	30
Min. Sound Output* (dBA / 10cm)	80
Frequency* (Hz)	2300 +/- 300
Tone Nature	Single
Operating Temperature (°C)	-40~ +85
Terminal	Pin
Housing Material	Noryl
Weight (g)	2

* Value applying rated voltage

Dimension (mm)

