

SYLPENDANT VINTAGE FLARE

SYLPENDANT VINTAGE FLARE E27

0044406



Product features

- A classic style non-integrated pendant for decorative and general lighting applications Premium fit and finish The black and brass colour combination metal housing and elegant glass cover helps the product stand-out in all kinds of interior settings Adjustable black fabric cable included, so you can create the drop to best suit the height of your room Applications: Perfect for kitchens, living rooms, dining rooms, hallways, restaurants, cafés, bars and galleries Easy-to-install and supplied with an E27 lamp holder Maximum recommended LED lamp wattage: 25W, lamp not included



PRODUCT OVERVIEW

Product name	SYLPENDANT VINTAGE FLARE E27
Technology	Accessory
Housing	Metal/plastic
Mount	Pendant surface
General application	Hospitality, Museums & Galleries, Office, Residential & Consumer, Retail
ETIM Class	EC001743
Warranty	3 years
Light colour	N/A
Light source included	Fixture without Lightsource
Electrical protection	Class I
Housing colour	Black
IP rating	IP20
IK rating	IK03
Product EAN number	5410288444062

DATA TABLE

General data

Product name	SYLPENDANT VINTAGE FLARE E27
Technology	Accessory
Housing	Metal/plastic
Mount	Pendant surface
General application	Hospitality, Museums & Galleries, Office, Residential & Consumer, Retail
ETIM Class	EC001743
Warranty	3 years

SYLPENDANT VINTAGE FLARE

SYLPENDANT VINTAGE FLARE E27
0044406

Optical data

Light colour	N/A
---------------------	-----

Electrical data

Light source included	Fixture without Lightsource
Mains voltage (V)	220-240V
Electrical protection	Class I
Glow Wire Test (°C)	650
Nominal Frequency (Hz)	50/60Hz

Physical data

Housing colour	Black
IP rating	IP20
IK rating	IK03
Nominal Product Length (mm)	1723
Nominal Product Width (mm)	127
Nominal Product Height (mm)	233
Weight (kg)	0.75

Packaging

Single packaging type	Carton
Product EAN number	5410288444062
Packaging single length / height (cm)	35.0
Packaging single width (cm)	35.0
Packaging single depth (cm)	25.0
DUN14 (outer)	05410288444062
Units per outer package	1
Packaging outer length / height (cm)	37.0
Packaging outer width (cm)	37.0
Packaging outer depth (cm)	27.0