


## Inset Kit LED IP44

INSET TREND KIT SW IP44 REFLED BA 36° NW DIM  
3001767



### Product features

- GU10 Housing with REFLED ES50 36° lamp included, Ideal for indoor application, Loop in - loop out box included



## PRODUCT OVERVIEW

Product name	INSET TREND KIT SW IP44 REFLED BA 36° NW DIM
Technology	LED
Cap/Base	GU10
Housing	Aluminium
Mount	Ceiling recessed mounting
Environment	Indoor
General application	Hospitality, Residential & Consumer
ETIM Class	EC001744
E-number FI	4270042
E-number SE	7468153
Warranty	3 years
Fixture luminous flux (lm)	345
Luminaire efficacy (lm/W)	76
LOR (%)	100
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Beam Angle (°)	40
Light source included	0029128
Total power consumption (W)	4.5
Control gear type	Electronic ballast
Dimming method	Mains: leading / trailing edge
Housing colour	Aluminium
IP rating	IP44/20
IK rating	IK02
Product EAN number	8711971017677

## DATA TABLE

### General data

Product name	INSET TREND KIT SW IP44 REFLED BA 36° NW DIM
Technology	LED
Cap/Base	GU10

## Inset Kit LED IP44

*INSET TREND KIT SW IP44 REFLED BA 36° NW DIM*  
3001767

<b>Housing</b>	Aluminium
<b>Mount</b>	Ceiling recessed mounting
<b>Environment</b>	Indoor
<b>General application</b>	Hospitality, Residential & Consumer
<b>ETIM Class</b>	EC001744
<b>E-number FI</b>	4270042
<b>E-number SE</b>	7468153
<b>Warranty</b>	3 years

### Optical data

<b>Fixture luminous flux (lm)</b>	345
<b>Luminaire efficacy (lm/W)</b>	76
<b>LOR (%)</b>	100
<b>Colour temperature (K)</b>	4000
<b>Light colour</b>	Neutral White
<b>CRI (Ra)</b>	80
<b>Adjustable chromaticity</b>	N
<b>Beam Angle (°)</b>	40

### Electrical data

<b>Light source included</b>	0029128
<b>Total power consumption (W)</b>	4.5
<b>Mains voltage (V)</b>	220-240V
<b>Control gear type</b>	Electronic ballast
<b>Transformer required</b>	Yes
<b>Dimming method</b>	Mains: leading / trailing edge
<b>Energy Efficiency Class (A-&gt;G) of contained light source</b>	F

### Physical data

<b>Housing colour</b>	Aluminium
<b>IP rating</b>	IP44/20
<b>IK rating</b>	IK02
<b>Diffuser finish</b>	Transparent
<b>Diffuser material</b>	Other
<b>Nominal Product Height (mm)</b>	100
<b>Nominal Product Diameter (mm)</b>	95
<b>Cutout Dimensions (W x L in mm or Diameter in mm)</b>	75
<b>Weight (kg)</b>	0.17
<b>Recessed Depth (mm)</b>	140

### Packaging

<b>Single packaging type</b>	Carton
<b>Product EAN number</b>	8711971017677
<b>Packaging single length / height (cm)</b>	13.0
<b>Packaging single width (cm)</b>	10.0
<b>Packaging single depth (cm)</b>	8.0
<b>DUN14 (outer)</b>	08711971017677
<b>Units per outer package</b>	1

## Inset Kit LED IP44

*INSET TREND KIT SW IP44 REFLED BA 36° NW DIM*

3001767

Packaging outer length / height (cm)	13.0
Packaging outer width (cm)	10.0
Packaging outer depth (cm)	8.0

## PHOTOMETRY

---

## TECHNICAL DRAWINGS

---

