

Shrink-fit extension

Version with cylindrical shank

diebold

Application:

For extending and reducing to smaller diameters.

Execution:

- With 3° angle.
- Clamping diameter for h6 shank tolerance.

Delivery:

1x shrink-fit extension; version with cylindrical shank.



Art. no.	23431 006
Brand	DIEBOLD
Manufacturer Part Number	75.501.106.01
Outer diameter	12 mm
Clamping diameter	6 mm
Cylinder diameter	11.8 mm
Tapered diameter	12 mm
Length	110 mm
Projecting length	63 mm
Max. adjustment travel	5 mm
Gross Weight	0.040 kg
Product Group	297