

Electronic pocket callipers

Digital ABS with adjustable measuring arm

Mitutoyo

Application:

For measuring stepped workpieces, for example

Execution:

- Digimatic
- ABSOLUTE system for reliable measurement
- adjustable measuring arm
- With thumb roller
- High-contrast display

Advantage:

- High resistance to water and dust (degree of protection IP67)
- For difficult-to-reach measurement tasks

Delivery:

Delivered in a box



Art. no.	32018 091
Brand	MITUTOYO
Manufacturer Part Number	573-70 1-20
Min./max. length measuring range in inches	0-6 in
Data transmission type	DIGIMATIC
IP protection class	IP 67
With drive wheel	Yes
Error limit	0.001 in
Length of jaw	95 mm
Design	Metric, Imperial
Digit height	10 mm
Length of cross tips	10 mm
Digit increment	0.01 mm
Digit increment in inches	0.0005 in
Type of locating	With locking screw
Preset function	No
With mm / inch switching	Yes
With automatic shut off	Yes
Battery designation	1,5 V SR44
Number of rechargeable batteries/batteries	1 PCS
Weight of rechargeable battery/battery	0.002 kg
Battery voltage	1.55 V
Type of rechargeable battery/battery	Silver oxide
Calibration Group	A
ISO	13385-1
Functions	ABS function, Absolute function, Origin (Dimension preset), Automatic switch-off
Gross Weight	0.535 kg
Product Group	3MA

EAN

4946368726731