

FIPLOCK® ONE T-Adapter

Conduit fitting system for highest requirements, suitable for FIPLOCK® PA6 / PA12

FIPLOCK® ONE T-Adapter

Info

New conduit fitting system with innovative locking system



Rail



Good chemical resistance



Flame-retardant



Halogen-free



Cold-resistant



Maximum vibration protection



Mechanical resistance



Assembly time



Low weight

Last Update (11.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

FIPLOCK® ONE T-Adapter



Optimum strain relief



Robust



Reliability



UV-resistant



Waterproof



Benefits

Very high tensile strength due to all around tooth system
 Ensures mounting safety due to integrated coding system
 Excellent IP rating
 Cost-saving due to quick and easy installation

Application range

Suitable for FIPLOCK® PA6 / PA12
 Demand of increased liquid tightness
 For indoor and outdoor use

Product features

All around locking mechanism due to 360° tooth system
 Locking mechanism with integrated coding system
 Extended sealing range across multiple corrugated conduit waves

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001176 ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001176 ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose
Certifications:	IEC EN 61386-23 EN 45545-2 HL3
Colour delivered:	Grey (RAL 7005) Black (RAL 9005), UV-resistant
Material:	PA 6 Halogen-free Fire behaviour according to UL 94V-0
Protection rating:	IP66/IP67/IP68/IP69
Temperature range:	-45°C to +120°C

Last Update (11.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

FIPLOCK® ONE T-Adapter

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

FIPLOCK® ONE T-Adapter

Article number	Nominal size	Hole Ø (mm)	Suitable for FIPLOCK® PA6 / PA12	Colour	Pieces / PU
FIPLOCK® ONE-TA black					
61804962	10-10-10	M4	10	black	10
61804963	12-12-12	M4	12	black	10
61804964	17-17-17	M5	17	black	10
61804965	23-23-23	M5	23	black	6
61804966	29-29-29	M5	29	black	6
61804967	36-36-36	M6	36	black	4
61804968	48-48-48	M6	48	black	4
FIPLOCK® ONE-TA grey					
61804969	10-10-10	M4	10	grey	10
61804971	12-12-12	M4	12	grey	10
61804972	17-17-17	M5	17	grey	10
61804973	23-23-23	M5	23	grey	6
61804974	29-29-29	M5	29	grey	6
61804975	36-36-36	M6	36	grey	4
61804976	48-48-48	M6	48	grey	4

Last Update (11.12.2022)

©2022 Lapp Group - Technical changes reserved

 Product Management www.lappkabel.de

 You can find the current technical data in the corresponding data sheet.
 PN 0456 / 02_03_16

FIPLOCK® ONE T-Adapter

