

Product information

26 13 200

Snipe Nose Side Cutting Pliers (Stork Beak Pliers)


DIN ISO 5745

- Elastic tips: dimensionally stable even when twisted
- Distortion-tolerant, elastic precision tips
- Half-round, long, tapered jaws
- With cutting edges for soft, medium-hard and hard wire
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 61 HRC
- Straight jaws
- Vanadium electric steel, forged, multi stage oil-hardened



General	
Article No.	26 13 200
EAN	4003773040590
Pliers	chrome-plated
Head	chrome-plated
Handles	plastic coated
Weight	169 g
Dimensions	200 x 52 x 14 mm
Standard	DIN ISO 5745
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Cutting capacities medium hard wire (diameter)	Ø 3.2 mm
Cutting capacities hard wire (diameter)	Ø 2.2 mm
Jaw thickness (joint) (T1)	9.5 mm
Tips width (W4)	3.0 mm
Tips thickness (T2)	2.5 mm
Jaw length (L3)	73.0 mm
Head width (W3)	18 mm



technical change and errors excepted

