

DTGN insert holder, negative right

For longitudinal turning with TN indexable insert



Application:

For longitudinal turning with TN indexable insert, 60°

Execution:

- Precision-manufactured steel support, burnished, hardened, adjustable clamping system, type T, pitch angle 90°, tip angle 60°, clearance angle 0°

Advantage:

- Universal application for facing and longitudinal turning with high feed depths and unfavourable conditions
- Negative body geometry ensures good stability and absorption of force for large cutting depths
- Wide adjustment range: Suitable for both finishing and rough machining
- Adjustable clamp minimises vibrations and ensures favourable power transmission

Art. no.	17684 099
Brand	WIDIA
Manufacturer Part Number	5696729
ISO name	DTGN R/L 2020 K16
Knife edge length	16 mm
Shaft height	20 mm
Shank width	20 mm
Length	125 mm
Programming size	25 mm
Suitable for indexable inserts	TN.. 1604..
Tool design	Right
Length of head	25 mm
Gross Weight	0.001 kg
Product Group	1XG

EAN

4050841486378