

Type ERICKSON collets

For ERICKSON system

ORION[®]

Application:


For clamping tools with straight shank.

Execution:

- For short chuck system ERICKSON sealing taper/sealing taper shank no. 23325.
- Multi-range collets for clamping the nominal diameter.
- Concentricity 20 µm.
- Clamp bridge -0.5 mm.

Delivery:

1x type ERICKSON collet.



Art. no.	23326 216
Brand	ORION
Manufacturer Part Number	23326216
Type	418E
Collet type	DK 10
Clamping diameter	10 mm
Min./max. clamping range	2.5-14.5 mm
Gross Weight	0.094 kg
Product Group	218

EAN

4039247157624