

Electronic micrometer

With large measuring range IP65

Mitutoyo

Application:

For measuring e.g. shank diameters, external dimensions of workpieces etc.

Execution:

- carbide-tipped measuring faces
- ABS function
- HOLD (measured value storage)
- Origin (measurement presetting)
- IP65

Advantage:

- Long battery life, approx. 2.4 years
- IP65

Delivery:

Includes box, wrench, battery, setting standard (from 25 mm), up to 50-mm measuring range with factory test certificate



Art. no.	32017 359
Brand	MITUTOYO
Manufacturer Part Number	293-357-30
Display	Digital
Min./max. length measuring range in inches	11-12 in
Digit increment	0.0001 in
Measuring surface diameter	6.3 mm
IP protection class	IP 65
Data transmission type	DIGIMATIC
Spindle clamping	Yes
Digit height	7.5 mm
Functions	ABS function, Hold-function (AE lock), Origin (Dimension preset), Preset function, Automatic switch-off
Min./max. measurement force	5-10 N
Number of rechargeable batteries/batteries	1 PCS
Battery designation	1,5 V SR44
DIN	863
Bracket depth	166 mm
Measuring spindle increments	6.35 mm
Calibration Group	D, E
Gross Weight	3.380 kg
Product Group	3MA

EAN

4946368695570