

## Ergo series 300 table trolley, load capacity 500 kg

Load area 1200x800 mm



### Application:

For safely and easily transporting goods, parts and materials.

### Execution:

- Powder-coated with MDF board
- Two fixed castors, two swivel castors with brake, castor diameter: 200 mm
- Spacing between the load areas: 580 mm
- Load capacity per load area: 250 kg
- 2 fixed castors and 2 swivel castors made of solid rubber 200x50 mm
- Load capacity of load areas: 250 kg each

### Advantage:

- No need to go far to find your tools - work equipment is provided directly at the workstation
- Non-marking tyres



<b>Art. no.</b>	<b>50291 458</b>
<b>Brand</b>	KONGAMEK
<b>Manufacturer Part Number</b>	KM337-ERGO
<b>Load-carrying capacity</b>	500 kg
<b>Length</b>	1110 mm
<b>Length x width x height</b>	1110 x 800 x 934 mm
<b>Load-carrying capacity of loading surfaces</b>	250 kg
<b>ESD-capable</b>	No
<b>Number of loading surfaces</b>	2
<b>Loading surface size</b>	1200 x 800 mm
<b>Loading surface length</b>	1200 mm
<b>Loading-surface width</b>	800 mm
<b>Height</b>	934 mm
<b>Number of fixed rollers</b>	2
<b>Number of steering rollers</b>	2
<b>With wheel lock</b>	Yes
<b>Wheel diameter</b>	200 mm
<b>Material of wheel</b>	Solid rubber
<b>Colour</b>	Blue
<b>Surface</b>	Powder-coated
<b>Gross Weight</b>	44.500 kg
<b>Product Group</b>	5AT

### EAN

7350074806880