

Parallel vice 80–150 mm, heavy-duty version

With rear opening action, made of grey cast iron

LEINEN

Version:

- High-quality grey cast iron with pearlitic texture
- Hardened, ribbed steel jaws can be swapped for smooth, ground steel jaws
- Smooth-running spindle with trapezoidal thread
- High-quality hammertone finish, green (similar to RAL 6011)

Advantage:

- Excellent clamping precision thanks to long, prismatic precision guide
- Spindle protected from dirt and damage by covering



Art. no.	51035 140
Jaws width	100 mm
Min./max. clamping width	0-140 mm
Clamp in depth	75 mm
Weight	17 kg
Colour	Green
Material	Grey cast iron