



**BE-7907 - BE-7940**

**ERGO™ TORX® and Tamper-Resistant TORX® Screwdrivers with Rubber Grip Double Handle TR7-TR40**



## PRODUCT DETAILS









- Screwdriver developed according to the scientific ERGO™ process
- For TORX® tamper-resistant head screws with safety pin
- Phosphate finished tip for higher accuracy
- three-component handle for maximum user comfort, soft material with ridged surface provides superior grip and greater force transmission
- Easy to choose the right tip with the colour-coded handle and permanent symbol on the domed end
- Flat face to prevent rolling away
- Integrated hanging hole
- High-performance alloy steel blade with chrome plating, entirely hardened for high protection against corrosion, long life tool
- Maximum comfort with minimum effort thanks to an ergonomic design
- 3-component comfortable handle giving an excellent grip
- Anti-roll flat face on handle



**Follow the Fish!**



## PRODUCT ATTRIBUTES

Product								
<b>BE-7907</b>	TR 7	1.97 mm	75 mm	3 mm	20 mm	122 mm	197 mm	31 g
<b>BE-7908</b>	TR 8	2.30 mm	75 mm	3 mm	17 mm	103 mm	178 mm	31 g
<b>BE-7909</b>	TR 9	2.48 mm	75 mm	3 mm	20 mm	122 mm	197 mm	31 g
<b>BE-7910</b>	TR 10	2.72 mm	75 mm	3 mm	20 mm	122 mm	197 mm	31 g
<b>BE-7915</b>	TR 15	3.26 mm	100 mm	4 mm	27 mm	122 mm	222 mm	57 g
<b>BE-7920</b>	TR 20	3.84 mm	100 mm	4 mm	27 mm	122 mm	222 mm	57 g
<b>BE-7925</b>	TR 25	4.40 mm	125 mm	5 mm	27 mm	122 mm	247 mm	70 g
<b>BE-7927</b>	TR 27	4.96 mm	125 mm	5 mm	27 mm	122 mm	247 mm	70 g
<b>BE-7930</b>	TR 30	5.49 mm	150 mm	6 mm	36 mm	122 mm	272 mm	119 g
<b>BE-7940</b>	TR 40	6.60 mm	150 mm	7 mm	36 mm	161 mm	311 mm	130 g

