

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0430310021](#)
Status: **Active**
Overview: [Micro-Fit Connector System](#)
Description: Micro-Fit 3.0 Crimp Terminal, Male, with Tin (Sn) Plated Phosphor Bronze Contact, 18 AWG, .073in / 1.85mm Max Insulation Outside Diameter, Reel

Documents:

Drawing (PDF)	Test Summary 430450005-TS-000 (PDF)
Product Specification 430450001-PS-KO-000 (PDF)	Test Summary TS-43045-001-001 (PDF)
Product Specification 430450001-PS-SP-000 (PDF)	Datasheet (PDF)
Product Specification PS-43045-001 (PDF)	RoHS Certificate of Compliance (PDF)
Packaging Specification PK-43031-001-001 (PDF)	

General

Product Family	Crimp Terminals
Series	43031
Application	Power, Wire-to-Wire
Comments	Part Number 430310021 is Designed for 18 AWG 1061 Style Wire or a .073/1.85 Maximum Insulation Outside Diameter
Crimp Quality Equipment Overview	Yes
Product Name	Micro-Fit Connector System
UPC	Micro-Fit 3.0 191128166102

Physical

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.061/g
Packaging Type	Reel
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.85mm max.
Wire Size AWG	18
Wire Size mm ²	0.75


Electrical

Current - Maximum per Contact	8.5A
-------------------------------	------

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-43031-001-001
Product Specification	430450001-PS-KO-000, 430450001-PS-SP-000, PS-43045-001
Sales Drawing	SD-43031-XXXX-001
Test Summary	430450005-TS-000, TS-43045-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[43031 Series](#)

Use With

Micro-Fit 3.0 Plug Housings [43020](#) , [43640](#)

Micro-Fit BMI Plug Housings [44300](#) ,
[46625](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
-------------	-----------

Extraction Tool for Micro-Fit Terminals	11030043
---	--------------------------

Insertion Tool for Micro-Fit 3.0 and CRC Male and Female Crimp Terminals, 20-30 AWG	638120800
---	---------------------------

Hand Crimp Tool for [638280200](#)
Micro-Fit 3.0 Female
Crimp Terminals,
0.75mm² and
18AWG (UL1061)
wires
FineAdjust Applicator [639025800](#)
for Micro-Fit 3.0
and Micro-Fit
Plus Terminals,
for 0.75mm²
and 18 AWG
(UL1061) Wires with
Insulation Diameter
1.40-1.85mm

This document was generated on 08/17/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION