

Touch panel - BTP 2043W



1050387

<https://www.phoenixcontact.com/pc/products/1050387>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Touch panel with 10,92 cm / 4,3"-TFT-display (analog resistive (polyester)), 480 x 272 pixel(s) (WQVGA), 262144 colors, Arm[®] Cortex[®]-A7, 700 MHz i.MX6 UL, 2x COM (RS-232/422/485), 1x USB 2.0, Typ A, 1x USB 2.0, Typ B, 1 x Ethernet (10/100 Mbps), RJ45, Windows[®] Embedded Compact 7 and user software: Visu+. (bus system: without)

Your advantages

- Visu+ RT integrated as standard in all BTP 2000 devices
- Connection to all relevant control systems, thanks to a large number of available drivers
- Developed for basic applications with attractive price/performance ratio
- 3 display sizes in 16:9 format

Commercial Data

Item number	1050387
Packing unit	1 pc
Minimum order quantity	1 pc
Product Key	DRCEBC
Catalog Page	Page 471 (C-6-2019)
GTIN	4055626666587
Weight per Piece (including packing)	331.7 g
Weight per Piece (excluding packing)	324 g
Customs tariff number	84715000
Country of origin	IN

Touch panel - BTP 2043W



1050387

<https://www.phoenixcontact.com/pc/products/1050387>

Technical Data

Product properties

Product type	Operator panel
--------------	----------------

Computer data

Processor	Arm® Cortex®-A7, 700 MHz i.MX6 UL
Operating system	Windows® Embedded Compact 7
RAM	512 MB DDR3 SDRAM
Data storage	eMMC, 4 GB
Slots	1x SD

Display

Display type	10,92 cm / 4,3"-TFT
Screen resolution	480 x 272 Pixel(s) (WQVGA)
Touch technology	analog resistive (polyester)
Display lighting type	LED
Brightness	400 cd/m ² , typical (adjustable)
MTBF	25000 h
Color spectrum	262144 colors
Reading angle left	70 °
Reading angle right	70 °
Reading angle top	50 °
Reading angle bottom	70 °

Software

User software	Visu+
---------------	-------

Interfaces

Interfaces	2x COM (RS-232/422/485)
	1x USB 2.0, Typ A
	1x USB 2.0, Typ B
Network	1 x Ethernet (10/100 Mbps), RJ45
Bus system	without

Electrical properties

Supply

Power supply unit	24 V DC ±15 %
Typical current consumption	0.17 A

Mounting

Mounting type	Front mounting
---------------	----------------

Material specifications

Touch panel - BTP 2043W



1050387

<https://www.phoenixcontact.com/pc/products/1050387>

Material front plate	Plastic
Housing material	Plastic

Ambient conditions

Degree of protection	IP66 (front), IP20 (back)
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)
Shock	DIN EN 60068-2-27
Vibration (operation)	DIN EN 60068-2-6

Dimensions

External dimensions

Width / Height / Depth	120 mm / 89 mm / 5 mm (Dimensions of the front plate)
------------------------	---

Installation dimensions

Width / Height / Installation depth	111 mm / 80 mm / 31.5 mm (Installation cutout)
-------------------------------------	--

Touch panel - BTP 2043W



1050387

<https://www.phoenixcontact.com/pc/products/1050387>

Approvals



EAC

Approval ID: RU*-DE*08.B.00004/18



EAC

Approval ID: RU*-DE*35.B.00394/20



cUL Listed

Approval ID: FILE E 196811



UL Listed

Approval ID: FILE E 196811

cULus Listed

Touch panel - BTP 2043W

1050387

<https://www.phoenixcontact.com/pc/products/1050387>



Classifications

ECLASS

ECLASS-9.0	27330201
ECLASS-10.0.1	27330201
ECLASS-11.0	27330201

ETIM

ETIM 8.0	EC001412
----------	----------

UNSPSC

UNSPSC 21.0	43211900
-------------	----------

Touch panel - BTP 2043W

1050387

<https://www.phoenixcontact.com/pc/products/1050387>



Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

Touch panel - BTP 2043W

1050387

<https://www.phoenixcontact.com/pc/products/1050387>



Accessories

Touch pen

Touch pen - TOUCH PEN - 2701379

<https://www.phoenixcontact.com/pc/products/2701379>



Touch pen for analog-resistive HMI, silver coated. Delivery includes self-adhesive pen holder.

PCB connector

PCB connector - MSTB 2,5/ 3-ST-5,08 - 1757022

<https://www.phoenixcontact.com/pc/products/1757022>



PCB connector, nominal cross section: 2.5 mm², color: green, nominal current: 12 A, rated voltage (III/2): 320 V, contact surface: Tin, type of contact: Female connector, number of potentials: 3, number of rows: 1, number of positions: 3, number of connections: 3, product range: MSTB 2,5/...-ST, pitch: 5.08 mm, connection method: Screw connection with tension sleeve, screw head form: L Slotted, conductor/PCB connection direction: 0 °, locking clip: - Locking clip, plug-in system: COMBICON MSTB 2,5, locking: without, mounting: without, type of packaging: packed in cardboard

Phoenix Contact 2022 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG

Flachsmarktstraße 8

D-32825 Blomberg

+49 (0) 5235-3 00

info@phoenixcontact.com