

MILAN S.r.l. a socio unico

Head Office – Export department:
 Viale Europa, 74
 20090 Cusago (MI) Italy
 T. +39 02 9039.4556-4158
 F. +39 02 9039.4551
 www.taskercables.com

Ufficio Commerciale e Centro Distribuzione
 Viale Europa 72 Strada F12
 20090 Cusago (MI) Italy
 T. +39 02 9039.0037-0059
 F. +39 02 9039.0049
 www.tasker.it

Technical Datasheet

✓
RoHS₂
2002/95/EC
2011/65/UE

tasker® C100 – 2x0,50 mm² Flat Audio Divisible Cable



A

B

CATEGORY **Polarized Flat Cable** (See Audio Catalogue)

- A:** Soft **PVC** Sheath, available in different colors.
Outer cable dimension 2,00 x 4,10 mm (±0,20) mm.
- B:** One conductor made of O.F.C. tinned copper and one of O.F.C. Red Copper. Formation with 0,20 mm wires.
Nominal cross section 2x0,50 mm².

CUSTOM This product is also available in **L.S.Z.H., PE, PUR.**

Conductors Properties

Conductor Resistance	45 Ω/Km ± 5%
Max Rated Voltage	49 V
Operative Temperature	-15/+70°C

USE	X	Indoor	Interno Edificio	INSTALLATION	X	Fixed	Fissa	INFORMATION	X	RoHS2 Compliant
Impiego	X	Outdoor Limited	Esterno Limitato	Posa	X	Flexible Limited	Flessibilità limitata	Informazioni	X	Ver.C / 16.06.16
		Outdoor Direct Burial	Esterno Interrato		X	Dynamic (Drag Chain)	Mobile in Catena			
						Dynamic (Torsion)	Mobile in Torsione			