

# GN 111.4 | Spiral retaining cables

Polyurethane and stainless steel



- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18

## RINGS (SUPPLIED NOT ASSEMBLED)

Stainless steel.

## CLAMPING PLATE

Stainless steel.


## SPIRAL CABLE

Polyurethane (PUR) black colour.

## FEATURES AND APPLICATIONS

GN 111.4 spiral retaining cables are mainly used in combination with the different types of self-locking pins.

The load values shown in the table have to be considered as purely indicative.



Code	Description	d1	d2	l1 min	l2 max	Static load with ring [N]	Static load without ring [N]	⚖️
GN.11391	GN 111.4-50-14	14*	1	50	250	50	60	10
GN.11392	GN 111.4-50-18	18**	1.3	50	250	60	60	10
GN.11393	GN 111.4-50-24	24	1.5	50	250	60	60	10
GN.11394	GN 111.4-100-14	14*	1	100	500	50	60	10
GN.11395	GN 111.4-100-18	18**	1.3	100	500	60	60	15
GN.11396	GN 111.4-100-24	24	1.5	100	500	60	60	15
GN.11397	GN 111.4-200-14	14*	1	200	1000	50	60	15
GN.11398	GN 111.4-200-18	18**	1.3	200	1000	60	60	15
GN.11399	GN 111.4-200-24	24	1.5	200	1000	60	60	18

\* Suitable for the following lock pins: GN 124 only Ø6, Ø8; GN 113.1, GN 113.3, GN 113.5, GN 113.6, GN 113.7, GN 113.8, GN 114.2, GN 114.3, GN 114.6 all the Ø.

\*\* Suitable for the following lock pins: GN 124 only Ø10, Ø12, Ø16.

Indexing and positioning elements