



**Part no.: 50022811**  
**TK 40X180.1**  
**Reflector**

Figure can vary

## Contents

- Technical data
- Dimensioned drawings

Part no.: 50022811 – TK 40X180.1 – Reflector

## Technical data

| <b>Mechanical data</b>                   |             |
|--|-------------|
| Design                                   | Rectangular |
| Mounting dimension, width                | 41 mm       |
| Reflection surface width                 | 36 mm       |
| Mounting dimension, height               | 181 mm      |
| Reflection surface height                | 176 mm      |
| Mounting dimension, thickness            | 8.2 mm      |
| Triple reflector size                    | 3 mm        |
| Reflector material                       | Plastic     |
| Material of base material                | Plastic     |
| Chemical designation, reflector material | PMMA8N      |
| Structure, active surface                | Triple      |
| Type of fastening                        | Adhesive    |

| <b>Environmental data</b>      |               |
|--------------------------------|---------------|
| Ambient temperature, operation | -40 ... 65 °C |

| <b>Certifications</b> |       |
|-----------------------|-------|
| Degree of protection  | IP 67 |

| <b>Classification</b> |          |
|-----------------------|----------|
| Customs tariff number | 90029000 |
| eCl@ss 8.0            | 27279203 |
| eCl@ss 9.0            | 27273601 |
| ETIM 5.0              | EC002467 |
| ETIM 6.0              | EC002467 |

## Dimensioned drawings

All dimensions in millimeters

