



LED COVER FOR POSITION SWITCH POSITION SWITCH METAL 3SE51, 2 LEDS, YELLOW/GREEN, 24 V DC, COLOR TURQUOISE

Product designation	cover with LEDs 24 V DC, for EN 50041 enclosures, metal, turquoise
---------------------	--

General technical data:

Degree of pollution	class 3
Shock resistance	30g / 11 ms
Vibration resistance	0.35 mm / 5g
Protection class IP	IP66/IP67
Explosion protection category for dust	none
Explosion protection category for gas	none

Enclosure:

Design of the housing	block, narrow
Coating of the enclosure	cathodic immersion coating

Drive Head:

Design of the operating mechanism	without
-----------------------------------	---------

Communication/ Protocol:

Design of the interface	without
-------------------------	---------

Ambient conditions:

Ambient temperature		
• during operation	°C	-25 ... +60
• during storage	°C	-40 ... +90

Supply voltage:

Type of voltage of the supply voltage	
• of the optional LED indicator	DC

Supply voltage	V	24
• of LED		

Installation/ mounting/ dimensions:

mounting position	any
Mounting type	screw fixing

Certificates/ approvals:

General Product Approval	Declaration of Conformity	Test Certificates	other
--------------------------	---------------------------	-------------------	-------



[Special Test Certificate](#)

[Confirmation](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SE51101AA00>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3SE51101AA00/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SE51101AA00&lang=en



last modified:

16.03.2015