

## Product information

# 71 01 200

## KNIPEX CoBolt®

### Compact Bolt Cutter



- Micro-structured cutting edge reduces slipping of the material from the jaws
- With gripping surface below the joint for gripping and pulling wires from Ø 1.0 mm
- With precision cutting edges for soft, hard and piano wire
- Cuts bolts, nails, rivets, etc. up to Ø 5.2 mm
- Efficient joint design ensures exceptional cutting performance with little effort
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



### General

Article No.	71 01 200
EAN	4003773033165
Pliers	black atramentized
Handles	plastic coated
Weight	335 g
Dimensions	200 x 41 x 15 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

### Technical details

Cutting capacities soft wire (diameter)	Ø 6 mm
Cutting capacities medium hard wire (diameter)	Ø 5.2 mm
Cutting capacities hard wire (diameter)	Ø 4.0 mm
Cutting capacities piano wire (diameter)	Ø 3.6 mm

*technical change and errors excepted*



with gripping surface below the joint for gripping and pulling wires from Ø 1.0 mm



Micro-structured cutting edge reduces slipping of the material from the jaws

