



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKE
Head type	Rotary head
Product compatibility	XCKJ
Associated body	ZCKJD31 ZCKJ1H29 ZCKJD31H7 ZCKJ9 ZCKJ11H7 ZCKJD39H29 ZCKJD39 ZCKJ21H7 ZCKJ21H29 ZCKJ1 ZCKJ2H7 ZCKJ21 ZCKJ2H29 ZCKJ9H29 ZCKJ11 ZCKJ11H29 ZCKJ1H7 ZCKJ2 ZCKJD31H29 ZCKJD39H7 ZCKJ9H7
Movement of operating head	Rotary
Type of operator	Stay put without operating lever stay put
Type of approach	Lateral approach, 2 directions

Complementary

Switch actuation	From left and right
Positive opening	With
Net Weight	0.42 lb(US) (0.19 kg)
Head material	Metal

Environment

Ambient air temperature for operation	-40...158 °F (-40...70 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Low temperature

Ordering and shipping details

Category	22411 - LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T
GTIN	00785901942474
Nbr. of units in pkg.	1
Package weight(Lbs)	0.8 lb(US) (0.36 kg)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.57 in (4 cm)
Package 1 width	3.31 in (8.4 cm)
Package 1 Length	1.81 in (4.6 cm)
Unit Type of Package 2	S02
Number of Units in Package 2	50
Package 2 Weight	22.49 lb(US) (10.201 kg)
Package 2 Height	5.91 in (15 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------