

PRODUCT-DETAILS

RC10-10

INS NYL RING TERM 12-10 No10 YELLOW



General Information

Extended Product Type	RC10-10
Product ID	7TAI029810R0018
EAN	5414363135173
Catalog Description	INS NYL RING TERM 12-10 No10 YELLOW
Long Description	Nylon Insulated Ring Terminal, Length 1.00 Inches, Width .37 Inches, Maximum Insulation .210, Bolt Hole #10, Wire Range #12-#10 AWG, Color Yellow, Copper, Tin Plated

Ordering

EAN	5414363135173
UPC	786210804385
Country of Origin	United States (US)
Selling Unit of Measure	each

Container Information

Package Level 1 Units	50 piece
Package Level 1 Width	4.69 in 119 mm
Package Level 1 Height	3.3 in 84 mm
Package Level 1 Depth / Length	6.3 in 160 mm
Package Level 2 Units	250 piece
Package Level 2 Width	9.3 in

	236 mm
Package Level 2 Height	8.7 in
	221 mm
Package Level 2 Depth / Length	15 in
	381 mm
Package Level 3 Units	2500 piece

Additional Information

Brand / Label	Sta-Kon
Color	Yellow
Effective Date	19751006
Material	Copper
Product Name	ELECTRICAL TERMINAL
Product Type	Nylon Insulated Ring Terminal
Special Functions	Self-insulated with high dielectric-strength nylon sleeves. An inner bronze insulation grip sleeve lengthens the flexing radius of the conductor and eliminates conductor creep.
Standards	UL E9809
Voltage Rating	600 V
Wire Size	12-10 AWG

Certificates and Declarations

Data Sheet, Technical Information	RC10-10
-----------------------------------	---------

Classifications

ETIM 6	EC001052 - Solderless copper terminals for copper conductors
ETIM 7	EC001052 - Solderless copper terminals for copper conductors
ETIM 8	EC001052 - Solderless copper terminals for copper conductors
UNSPSC	39121432
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4603 >> Electrical terminals

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Compression & Mechanical Connectors

