


Fluorescent T8 (Meat)

F58W T8 176 FoodStar Meat
0001818

Product features

- Features a specifically tailored spectrum that complements the natural colours of meats



PRODUCT OVERVIEW

| | |
|----------------------------|--------------------------------|
| Product name | F58W T8 176 FoodStar Meat |
| Technology | Fluorescent |
| Lamp shape | Tubular shape |
| Type | T8 |
| Cap/Base | G13 |
| Lamp finish | Frosted/Coated |
| Fixture rating | Open |
| General application | SPG |
| ETIM Class | EC000108 |
| E-number FI | 4940477 |
| E-number Norway | 3815461 |
| Colour temperature (K) | 3000 |
| Light colour | Foodstar Meat |
| CRI (Ra) | 84 |
| Wattage (W) | 58.00 |
| Product Voltage (V) | 110 |
| Dimmable | Yes |
| Dimming method | Mains: leading / trailing edge |
| Average life (Nominal) (h) | 24000 |
| Product EAN number | 5410288018188 |

DATA TABLE

General data

| | |
|---------------------|---------------------------|
| Product name | F58W T8 176 FoodStar Meat |
| Technology | Fluorescent |
| Lamp shape | Tubular shape |
| Type | T8 |
| Cap/Base | G13 |
| Lamp finish | Frosted/Coated |
| Fixture rating | Open |
| General application | SPG |

Fluorescent T8 (Meat) *F58W T8 176 FoodStar Meat* 0001818

| | |
|-----------------|----------|
| ETIM Class | EC000108 |
| E-number FI | 4940477 |
| E-number Norway | 3815461 |

Optical data

| | |
|--|---------------|
| Ambient temperature for maximum luminous flux (°C) | 25 |
| Colour temperature (K) | 3000 |
| Light colour | Foodstar Meat |
| CRI (Ra) | 84 |
| Adjustable chromaticity | N |

Electrical data

| | |
|-----------------------------------|--------------------------------|
| Wattage (W) | 58.00 |
| Watt (Rated) - High frequency (W) | 50.00 |
| Current (A) | 0.670 |
| Product Voltage (V) | 110 |
| Control gear required | Yes |
| Transformer required | No |
| Dimmable | Yes |
| Dimming method | Mains: leading / trailing edge |
| Drive current (mA) | 670 |
| kWh per 1000 hours burning time | 69 |

Lifetime data

| | |
|----------------------------|-------|
| Average life (Nominal) (h) | 24000 |
|----------------------------|-------|

Physical data

| | |
|-------------------------------------|---------------|
| Nominal Product Length (mm) | 1500.0 |
| Nominal Product Diameter (mm) | 26 |
| Max. Length base to base (mm) - A | 1500.0 |
| Length base to pin Min-Max (mm) - B | 1504.7-1507.1 |
| Max. Lamp Length (mm) - C/L | 1514.2 |
| Max. Lamp Diameter (mm) - D | 28.0 |
| Weight (kg) | 0.2 |

Packaging

| | |
|---------------------------------------|----------------|
| Single packaging type | Carton |
| Product EAN number | 5410288018188 |
| Packaging single length / height (cm) | 151.1 |
| Packaging single width (cm) | 2.9 |
| Packaging single depth (cm) | 2.8 |
| DUN14 (outer) | 15410288018185 |
| Units per outer package | 25 |
| Packaging outer length / height (cm) | 154.5 |
| Packaging outer width (cm) | 15.5 |
| Packaging outer depth (cm) | 15.0 |

Fluorescent T8 (Meat) *F58W T8 176 FoodStar Meat* 0001818

Safety data

| | |
|--|--------------|
| Lamp mercury content (mg) | 2.80 |
| Breakage cleaning instructions | Applicable |
| Recommendation for disposal at end of life | Applicable |
| Special purpose lamp | Yes |
| Intended purpose | Food display |
| Suitable for household illumination | No |

TECHNICAL DRAWINGS

