

## SYLPENDANT BRASS

*SylPendant Brass*

0043372



### Product features

- Sleek and compact metal pendant with the E27 socket, designed specifically to enhance the aesthetic of the product. Modern and versatile design. Perfect for Sylvania lampnaire range - ToLEDo™ Mirage, ToLEDo™ Radiance, ToLEDo™ Vintage, ToLEDo™ Retro and ToLEDo™ LifeStyle. Premium fit and finish. Sleek and compact black metal pendant with E27 socket, designed specifically to enhance the aesthetic of the product (only glass and metal visible). Maximum cord length 1450mm. Maximum rated LED lamp wattage = 25W.



### PRODUCT OVERVIEW

Product name	SylPendant Brass
Technology	Accessory
General application	Hospitality, Museums & Galleries, Office, Residential & Consumer, Retail
ETIM Class	EC001743
Warranty	3 years
Fixture luminous flux (lm)	N/A
Electrical protection	Class I
IP rating	IP20
IK rating	IK02
Product EAN number	5410288433721

### DATA TABLE

#### General data

Product name	SylPendant Brass
Technology	Accessory
General application	Hospitality, Museums & Galleries, Office, Residential & Consumer, Retail
ETIM Class	EC001743
Warranty	3 years

#### Optical data

Fixture luminous flux (lm)	N/A
----------------------------	-----

#### Electrical data

Mains voltage (V)	220-240V
Electrical protection	Class I

#### Physical data

IP rating	IP20
IK rating	IK02
Nominal Product Length (mm)	1650
Nominal Product Width (mm)	43

## SYLPENDANT BRASS

*SylPendant Brass*

0043372

Nominal Product Height (mm)	74
Weight (kg)	0.3

### Packaging

Single packaging type	Mix blister(20% carton, 80% pl
Product EAN number	5410288433721
Packaging single length / height (cm)	10.5
Packaging single width (cm)	10.5
Packaging single depth (cm)	13.0
DUN14 (outer)	15410288433728
Units per outer package	4
Packaging outer length / height (cm)	23.0
Packaging outer width (cm)	23.0
Packaging outer depth (cm)	16.0

## TECHNICAL DRAWINGS

