


Myriad Adjustable Round - Black with White bezel

MYRIAD ADJ ROUND BLACK 4000K PHDIM WHITE BEZ
2056220



Product features

- The Myriad Adjustable Round recessed spotlight is a high efficient accent downlight, fixture color RAL 9005 - Jet black, correlated colour temperature of 4000K, color rendering index Ra97, fixture lumen 684lm, total power consumption 10W, luminaire efficacy 68 lm/W, nominal light beam angle 24°, mains voltage 230-240V~ AC, control technology type: leading edge/trailing edge phase dim, product length 76mm, width 76mm, height 115mm, cut-out dimension 76mm, IP rating IP20, 5 years warranty.



PRODUCT OVERVIEW

Product name	MYRIAD ADJ ROUND BLACK 4000K PHDIM WHITE BEZ
Technology	LED
Housing	PC Polycarbonate
Mount	Ceiling recessed mounting
Environment	Indoor
General application	Hospitality, Office, Residential & Consumer, Retail
ETIM Class	EC001744
Warranty	5 years
Fixture luminous flux (lm)	684
Luminaire efficacy (lm/W)	68
LOR (%)	100
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	90
Colour Variation Initial (SDCM)	SDCM3
Beam Angle (°)	24
Photobiological Risk Group	RG1
Total power consumption (W)	10
Electrical protection	Class II
Control gear mounting	Integral
Housing colour	Black
IP rating	IP20
IK rating	IK02
Product EAN number	5025768562206

DATA TABLE

General data

Product name	MYRIAD ADJ ROUND BLACK 4000K PHDIM WHITE BEZ
Technology	LED
Housing	PC Polycarbonate
Mount	Ceiling recessed mounting

Myriad Adjustable Round - Black with White bezel

MYRIAD ADJ ROUND BLACK 4000K PHDIM WHITE BEZ
2056220

Environment	Indoor
General application	Hospitality, Office, Residential & Consumer, Retail
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001744
Warranty	5 years

Optical data

Fixture luminous flux (lm)	684
Luminaire efficacy (lm/W)	68
LOR (%)	100
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	90
Colour Variation Initial (SDCM)	SDCM3
Adjustable chromaticity	N
Beam Angle (°)	24
Distribution type	Symmetric
Photobiological Risk Group	RG1

Electrical data

Total power consumption (W)	10
Mains voltage (V)	230-240V
Electrical protection	Class II
Control gear mounting	Integral
Transformer required	Yes
Drive current (mA)	250
Energy Efficiency Class (A->G) of contained light source	E
Nominal Frequency (Hz)	50/60Hz

Lifetime data

Lifespan L70 B50	100000
Lifespan L80 B20	100000
Lifespan L90 B10	68500

Physical data

Housing colour	Black
IP rating	IP20
IK rating	IK02
Nominal Product Width (mm)	76
Nominal Product Height (mm)	115
Cutout Dimensions (W x L in mm or Diameter in mm)	76
Max. Lamp Diameter (mm) - D	90
Weight (kg)	0.38
Recessed Depth (mm)	115


Packaging

Single packaging type	Carton
-----------------------	--------

Myriad Adjustable Round - Black with White bezel MYRIAD ADJ ROUND BLACK 4000K PHDIM WHITE BEZ 2056220

Product EAN number	5025768562206
Packaging single length / height (cm)	17.5
Packaging single width (cm)	15.0
Packaging single depth (cm)	17.5
DUN14 (outer)	05025768562206
Units per outer package	1
Packaging outer length / height (cm)	17.5
Packaging outer width (cm)	15.0
Packaging outer depth (cm)	17.5

PHOTOMETRY



TECHNICAL DRAWINGS

