

## collet chuck DIN6343 173E, round

**FAHRION®**  
FAR BEYOND PRECISION

### Execution:

- hardened and ground
- clamping bridge max. 0.1 mm of the nominal diameter
- concentricity
- $\varnothing$  1-10 mm  $\leq$  20  $\mu$ m
- $\varnothing$  11-30 mm  $\leq$  30  $\mu$ m
- $\varnothing$  31-60 mm  $\leq$  40  $\mu$ m
- up to  $\varnothing$  8 mm smooth bore, from  $\varnothing$  8.5 mm with crosswise grooves
- Other designs and complete sets can be supplied on request.



<b>Art. no.</b>	<b>23327 015</b>
<b>Brand</b>	FAHRION
<b>Manufacturer Part Number</b>	10128010150
<b>Outer diameter</b>	60 mm
<b>Diameter</b>	48 mm
<b>Length</b>	94 mm
<b>Clamping diameter</b>	1.5 mm
<b>Profile shape</b>	Round and smooth
<b>DIN</b>	173
<b>Diameter 2</b>	48 mm
<b>Gross Weight</b>	0.672 kg
<b>Product Group</b>	235

### EAN

4054631006050