

Linear scales

with ABSOLUT system

Application:


In conjunction with the digital display units KA counter 39979010 or 39979020 for retrofitting manual processing machines such as lathes or milling machines.

Version:

- Digital length measuring system
- Degree of protection IP67
- Connector made of metal

Advantage:

- ABSOLUTE system, eliminates the need for a reference.



Art. no.	39979 310
Distance between centre and drill hole	358 mm
Distance between centre and drill hole 2	342 mm
Min./max. operating temperature	0 to 45 °C
Error of measurement for length (+/-)	+/- 5 µm
Effective measuring range	200 mm
Functions	Absolute function
Number of rechargeable batteries/batteries	0
Max. traverse path of measuring head	220 mm
Total length of linear measuring rod	378 mm
Power-lead length	3.4 m
Measuring method	Electromagnetic induction system
Approval mark	GS - TÜV Rheinland
IP protection class	IP 67
Signal period	20 µm
Power supply	5 V/DC
Adjustment speed	50 m/min

EAN-Code

4946368854151