

## Digital current clamp CM 1-2

for AC current up to 400 A, additional measurement functions

**BENNING**

### Application:

For measurement in electrical installations.

### Delivery:

Includes measuring leads

|   |                   |
|---|-------------------|
| <b>Art. no.</b>   | <b>75024 310</b>  |
| <b>Brand</b>  | BENNING           |
| <b>Manufacturer Part Number</b>                         | 044062            |
| <b>Model</b>  | CM 1-2            |
| <b>Display range</b>                                    | 2000 digits       |
| <b>Measuring accuracy</b>                               | +/- 1 %           |
| <b>Min./max. test voltage (DC)</b>                      | 0.1 V/AC-600 V/AC |
| <b>Min./max. test voltage (AC)</b>                      | 0.1 V/AC-600 V/AC |
| <b>Min./max. alternating current of measuring range</b> | 0.1 A-400 A       |
| <b>Continuity testing</b>                               | Yes               |
| <b>Diode testing</b>                                    | No                |
| <b>Min./max. electrical-resistance measuring range</b>  | 0.1 Ohm-20 MOhm   |
| <b>Max. collet opening</b>                              | 30 mm             |
| <b>Memory function</b>                                  | HOLD              |
| <b>Measuring procedure</b>                              | RMS               |
| <b>Overvoltage protection category</b>                  | CAT III/600 V     |
| <b>Length x width x height</b>                          | 190 x 70 x 38 mm  |
| <b>EN standard</b>                                      | 61010             |
| <b>Gross Weight</b>                                     | 0.473 kg          |
| <b>Product Group</b>                                    | 7AH               |



### EAN

4014650440624