

PNOZ s30 24-240VACDC 2 n/o 2 n/c

750330



Technical details

Approvals:	CE;cULus Listed;TÜV;CCC
Application options:	Speed monitoring;Standstill monitoring
Operating modes:	Automatic reset;Manual reset;Monitored manual reset
Standards:	EN 1088;EN 60204-1;EN 62061;EN 954-1;EN ISO 10218-1;VDI 2854
Supply voltage (V):	24,0 - 240,0
Supply voltage type:	AC/DC
Terminal type:	Screw terminal
Max. current at DC13 I (6 cycles/min):	4.0 A
Width dimension:	45.0 mm
Height dimension:	98.0 mm
Depth dimension:	120.0 mm
Gross weight:	428 g
Net weight:	427 g
Ambient temperature:	-20 - 55 °C