


ROLINE UTP Patch Cord, Cat.6, green, 3.0 m

Product No.	21.15.1553
Manufacturer	ROLINE
Manufacturer No.	21.15.1553
EAN (single piece)	7611990156375



Cat.6

U/UTP

Patch cable for networking connections between devices. Prepared unshielded Twisted Pair cable with RJ-45 connectors on both ends. Durable due to moulded kink protection. Flexible cable, suitable for narrow bending. High quality plugs with gold plated contacts. Contact settings 1:1, in accordance with the EIA/TIA 568 standard. Construction: 4-pair stranded copper wire.

For a structured cabling system we recommend to use the following components: ROLINE Cat.6 UTP Cable, Solid Wire, AWG23: 21.15.0990 (100 m), 21.15.0991 (300 m); ROLINE Cat.6 Flush Mount Wall Jack, unshielded: 25.16.8494 (white), 25.16.8500 (ivory); ROLINE Cat.6 Surface Mount Wall Jack, unshielded: 25.16.8394 (white), 25.16.8395 (ivory); ROLINE Cat.6 19" Patch Panel, 24 Ports, unshielded: 26.11.0355 (light grey), 26.11.0362 (black); ROLINE Cat.6 UTP Patch Cord, grey, 5 m: 21.15.0935. The accredited German laboratory GHMT has tested and certified this product combination, in a Channel of 100 meters, as being compliant to Class E specifications; certificate no. z2329b-10-E (with flush mount)/z2330b-10-E (with surface mount).

Technical specifications

Manufacturer	ROLINE
Product group	Twisted Pair Cable

Product type	UTP Patch Cables
Colour	green
Length	3 m
Shield type	UTP
Transfer quality	Cat6 / Class E
Impedance	100 Ohm
Quantity of wires	8
Conductor type	Wire
Crossed	No
Colour (Spout)	green
Cable LSOH	No
Connector Type RJ45	Standard