Heavy Duty Connector Housings

multicomp PRO

Specifications

|	
Surface	: Powder-Coated
Material	: Aluminium Die-Cast
Colour	: Grey
Lever Material	: Metal Galvanized / Nickel plating
Hoods and Housings Seal	: NBR
Temperature Range	: -40°C to +125°C
IP Rating	: IP65

Housing, Bulkhead Mount

Diagram

MP009396

MP009397

Part Number	Description
MP009396	1 Locking Lever
MP009397	1 Locking Lever with Plastic Cover

Housing, Surface Mount

MP009398

Dimensions : Millimetres

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicomp PRO

Page <1>   14/05/22   V1.0

MP009400

MP009401

Part Number	Description
MP009398	1 Locking Lever 2×M25
MP009400	1 Locking Lever 2×M25 with Plastic Cover
MP009401	1 Locking Lever, M25 with Plastic Cover

Dimensions : Millimetres

Part Number Table

Description	Part Number
Housing, H16A, Metal, Bulkhead Mount, 1 Locking Lever	MP009396
Housing, H16A, Metal, Bulkhead Mount, 1 Locking Lever with Plastic Cover	MP009397
Housing, H16A, Metal, Surface Mount, 1 Locking Lever, 2×M25	MP009398
Housing, H16A, Metal, Surface Mount, 1 Locking Lever, 2×M25 with Plastic Cover	MP009400
Housing, H16A, Metal, Surface Mount, 1 Locking Lever, M25 with Plastic Cover	MP009401

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicomp PRO

Page <2>

14/05/22   V1.0