

Product information

03 05 160

Combination Pliers

DIN ISO 5746

- With gripping zones for flat and round material, suitable for versatile use
- With cutting edges for soft and hard wire
- Long cutting edges for thicker cables
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 60 HRC
- Special tool steel, forged, multi stage oil-hardened



General	
Article No.	03 05 160
EAN	4003773039518
Pliers	chrome-plated
Head	chrome-plated
Handles	with multi-component grips
Weight	222 g
Dimensions	160 x 46 x 20 mm
Standard	DIN ISO 5746
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Cutting capacities medium hard wire (diameter)	Ø 3.1 mm
Cutting capacities hard wire (diameter)	Ø 2.0 mm
Cutting capacity copper cable, multiple-stranded	Ø 10.0 mm
Cutting capacity copper cable, multiple-stranded	16.0 mm ²

technical change and errors excepted