


ART.: 8425483173410

AS425 LED WIDE FLOOD REFLECTOR



Art.: 8425483173410, AS425 LED, 20W, 4000K, Driver static, Direct / wideflood (2 x 30°-37°), White, LED track light for interior, including: Extruded aluminum profile and die-cast aluminum spotlight housing, powder-coated, Tilting and turning spotlight head, High-brilliance spherical faceted reflector for maximum lamp performance and neutral colour rendering, Bayonet-closure ring for a toolless replacement of the reflector and the louvre, Reflector in Wide Flood design Colour rendering index Ra > 90, Colour tolerance according to MacAdam ≤ 3 SDCM Universal tri-phase adaptor included, Complete with electric converter, Toolless mounting, Complete with clear safety glass pane

Connected load	20 W
Luminous flux	2280 lm
Efficiency	114 lm/W
Colour temperature	4000K
Colour rendering (CRI)	80
IP class	20
Nominal voltage	220 – 240 V
Colour	RAL 9010

