

Die, HSSE MF right, pre-slotted and 2 thread chamfer for universal use up to 1300 N/mm²

ORION[®]

Application:

For cutting fine metric threads externally in the material groups of steel, stainless steel, non-ferrous metals and special alloys up to a strength of 1300 N/mm².

Execution:

- right die. tol. 6 g with spiral point, nitrided, pre-slotted and 2.0 pitch

Advantage:

- standard geometry with excellent price/performance ratio

Art. no.	13447 103
Brand	ORION
Manufacturer Part Number	13447 103
Thread type	Metric fine thread
Cutting material	HSSE
Tolerance of dies	6 g
Thread type x nominal diameter	MF10
Pitch	1 mm
Outer diameter	30 mm
Height	11 mm
Cutting direction	Right-hand cutting
Gross Weight	0.042 kg
Product Group	1DC



EAN

4039247073993